

## Stainless Steel Wall Mounted Eyewash Fountain



Product Code: S0440-AS

This stainless steel eyewash fountain is manufactured with a stainless steel bowl and stainless steel wall bracket for unbeatable ruggedness and durability. The unit is wall mounted allowing it to be mounted at an appropriate height for your employees. This stainless steel wall mounted eye wash fountain can be installed in most locations thanks to its diminutive proportions.

The wall mounted stainless steel eye wash units are constructed from robust materials and are designed to last, while the vibrant yellow spray heads aid visibility in emergency situations where vision may be impaired. The unit is easily activated by the high-viz, low resistance push handle. The spray heads are protected from debris by flippable dust covers.

When installing your stainless steel eye wash fountain, you must ensure that it is mounted between 838mm and 1,143mm from the floor, in order to comply with ANSI regulations. Each unit comes with an inspection tag for weekly functional testing, as well as a 32mm waste.

### Delivery

From stock 1 to 2 working days delivery time

Orders placed before 11.30am will be despatched for delivery next working day, or two working days if ordered after 11.30am

### Tech specs

Bowl diameter: 300mm

Bowl material: stainless steel

Wall bracket: stainless steel

Waste fitting: 32mm, chrome-plated brass

Water pressure: 2.07 - 6.21 bar

Flow Rate: 23.47 litres per minute

Ball valve: 1/2" stainless steel stay-open ball valve with 50 mesh inline strainer, brass 1/2" male BSP connector

Handle: stainless steel push handle

Spray heads: yellow ABS plastic spray heads with flip pen covers, internal flow controls and filters

### Extras

Your wall mounted eye wash fountain with stainless steel bowl is compatible with the following accessories:

[32mm chrome-plated brass trap](#)

### What is ANSI compliance?

The American National Standards Institute (or ANSI) is a private organisation that exists to oversee the development and use of standards both in the US and worldwide.

As far as safety eye wash is concerned, the ANSI regulation states, among other things, that the water should be delivered at a rate of 11.4 litres per minute for 15 minutes at a temperature between 16-38°C. [See our guide to the ANSI regulations](#) for further details on the advised location of safety stations and a thorough maintenance programme.

### Related products

You may also be interested in our [economy wall mounted eyewash stations](#), which comes with a plastic bowl. We also sell a [portable eye wash stations](#) for use in isolated areas where there is no access to potable water.

\*\*All pictures shown are for illustration purpose only and may be subject to change without notice. Actual product may vary due to product enhancement. All dimensions shown are for guidance only and may be subject to change or alteration without notice. All items manufactured or purchased separately from a third party to fit our products should be checked against the actual dimensions of the physical product before purchase. We will not be liable for third party costs and consequential loss associated with the items not fitting third party components.\*\*